



Swift Solution

ULTRAVELOX

Designed for Tough Pharma Cleaning



**Complete Range of Pharma
Cleaning Machinery**

AUTOMATIC AHU PRE FILTER CLEANING & DRYING MACHINE



Features :

- Three Models available depends upon productivity requirement by customer.
 - 1) one filter in one cycle time.
 - 2) Two filter in one cycle time.
 - 3) Three filter in one cycle time.
- Complete SS304 Frame & Cover.
- Full fills CGMP & FDA Audit Requirement.
- FLP & NON FLP Models available.
- Pre filter up to 610*610*355 mm can be effectively cleaned & Dried.
- PLC & HMI Controlled Electric panel.
- Multi process done in single chamber.
- Automatic Door open & close.
- Wet scrubber arrangement for exhaust dust control.
- Dual programme 1) Only dusting & 2) Dusting, Washing & drying.

Process :

- Compressed Air Dedusting.
- Pressure Wash.
- Compressed air flow.
- Hot air Blow.
- Centrifuge High speed spinning for Drying.

Advantage :

- Cleaning & Drying in Single Chamber.
- No Human Skill Requirement.
- Less Space required compared to conventional Process.
- Pollution controlled Cleaning & Drying.
- No Filter movement by operator like moving to dry chamber or keeping in sun light.
- High Clean & dry filter result in good indoor air quality & environment.

Application :

- Formulation
- Bulk Drug & Intermediates..
- Electronic & Space Application.

HIGH PRESSURE WASHER FOR PHARMA FORMULATION



- Mainly used for FBD Bowl Cleaning, Double cone blender, Coating Pan Cleaning, Mixer & RMG Cleaning.
- Full fills CGMP & FDA Audit Requirement.
- Pressure 150 Bar/10 LPM, 3HP – 1 Phase.
- Slow speed Motor with Auto cut off system.
- Heavy Duty system with weight 34 Kg.
- Wetted parts in Brass & SS.
- Heavy duty Rotomold Frame long life.
- In build Detergent tank.
- Wetted Parts SS316 Available on request

HIGH PRESSURE REACTOR CLEANING SYSTEM

- Complete SS304 Frame & Cover – FLP Model
- Full fills CGMP & FDA Audit Requirement.
- Pressure 150 Bar/15 LPM, 5HP
- Mainly used for Reactor Cleaning, Centrifuge cleaning, Filter press cleaning
- Wetted parts in Brass & SS.
- Available in complete SS316 Version.
- Less Water Consumption.



ELECTRIC HOT WATERJET CLEANING SYSTEM

- Complete SS304 Frame & Cover.
- Full fills CGMP & FDA Audit Requirement.
- Pressure 150 Bar/15 LPM, 5HP & 140Bar/9LPM, 3 HP Model Available.
- Mainly used for Formulation process Machinery cleaning. With Temperature 70 Degree
- Wetted parts in SS316 available on Request.
- Available in complete SS316 Version.
- Less Water Consumption.



STEAM CLEANER



- Complete SS304 Frame & Cover.
- Full fills CGMP & FDA Audit Requirement.
- Pressure 12 Bar/15 LPM, 9 Kw.
- Dry saturated Steam 188 Degree.
- Less Water Consumption.
- washing, sanitizing and drying done in a single process.
- 5% Water consumption, Results in water saving & Waste water Disposal.

CHANGE PARTS CLEANING SYSTEM



- Complete SS304 Frame & Cover.
- Full fills CGMP & FDA Audit Requirement.
- High pressure washing high Cleanliness level & level water usage.
- Hot water up to 80 Degree & 120 Deg Hot air Blower.
- washing, sanitizing and drying done in a single process.



TRAY WASHING SYSTEM

- Complete SS304 Construction.
- Full fills CGMP & FDA Audit Requirement.
- Multi stage washing, Rinsing & Drying.
- SS trays, Bins & Container can be cleaned.
- washing, sanitizing and drying done in a single process.



ULTRAVELOX PRIVATE LIMITED

Plot NO: 267, 7th Main Road,

SIDCO Industrial Estate Thirumudivakkam, - Chennai – 600 044.

E-mail : marketing@ultravelox.in

Mobile : 9445356642 / 6381576995 / 9445626642

Web site : www.ultravelox.in